## **GEL Tape**

Item	W (mm) $\times$ L (mm) $\times$ T (mm)
GT-1	10 × 1,000 × 1
GT-2	20 × 1,000 × 1
GT-3	10 × 1,000 × 2
GT-4	20 × 1,000 × 2
GT-5	10 × 1,000 × 3
GT-6	20 × 1,000 × 3

Custom size could be available.

## [Notes] • Before use, remove dust from the object.

- · Attach with even pressure after removing the separation liner paper.
- · Apply sufficient pressure to securely attach PSA (pressure-sensitive adhesive).
- · Powder is applied to the surface of GEL.