


Fair-Rite Product's Catalog Part Data Sheet, 4052077111 Printed: 2013-07-03









Part Number: 4052077111

Frequency Range: Low Permeability, High Saturation 52 (ui=250) material

Description: 52 ROD

Application: Inductive Components

Where Used: Open Magnetic Circuit

Part Type: Rods


Mechanical Specifications

Weight: .230 (g)

Part Type Information

Pressed Fair-Rite rods are used extensively in high-energy storage designs. These rods can also be used for inductive components that require temperature stability or have to accommodate large dc bias requirements.

- -The 'A' dimension can be centerless ground to tighter tolerances.
- -Figure 2 rods have a 0.6 mm (.024") maximum chamfer on the end faces.
- -For frequency tuned rod designs see section Antenna/RFID Rods.
- -For any rod requirement not listed here, feel free to contact our customer service group for availability and pricing.



Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com

Fair-Rite Product's Catalog Part Data Sheet, 4052077111 Printed: 2013-07-03









Mechanical Specifications

Dim	mm	mm	nominal	inch
		tol	inch	misc.
Α	2.00	±0.13	0.079	-
В	-	-	-	
С	15.00	±0.45	0.591	-
D	ı	ı	-	-
Е	ı	ı	-	-
F	ı	ı	-	-
G	ı		-	-
Н			-	-
J			-	-
K	-	-	-	-

Electrical Specifications

Ziodiidai Opodiidaidiid			
Typical Impedance (Ω)			
Electrical Properties			

Land Patterns

V	W	Х	Υ	Z
-	-	-	-	-
-	-	-	-	-

Winding Information

Turns	Wire	1st Wire	2nd Wire
Tested	Size	Length	Length
-	-	-	-

Reel Information

Tape Width	Pitch	Parts 7 "	Parts 13 "	Parts 14 "
mm	mm	Reel	Reel	Reel
-	-	-	-	-

Package Size

Pkg Size
-
(-)

Connector Plate

# Holes	# Rows
-	-

Legend

+ Test frequency

Preferred parts, the suggested choice for new designs, have shorter lead times and are more readily available.

The column H(Oe) gives for each bead the calculated dc bias field in oersted for 1 turn and 1 ampere direct current. The actual dc H field in the application is this value of H times the actual NI (ampere-turn) product. For the effect of the dc bias on the impedance of the bead material, see figures 18-23 in the application note How to choose Ferrite Components for EMI Suppression.

A 1/2 turn is defined as a single pass through a hole.

∑I/A - Core Constant

A_e: Effective Cross-Sectional Area

 A_{I} - Inductance Factor $\left(\frac{L}{N^{2}}\right)$

I e: Effective Path Length

Ve: Effective Core Volume

NI - Value of dc Ampere-turns

N/AWG - Number of Turns/Wire Size for Test Coil



Fair-Rite Product's Catalog Part Data Sheet, 4052077111 Printed: 2013-07-03







Ferrite Material Constants

Specific Heat 0.25 cal/g/°C

Coefficient of Linear Expansion 8 - 10x10⁻⁶/°C

Tensile Strength 4.9 kgf/mm²


Compressive Strength 42 kgf/mm²

Young's Modulus 15x10³ kgf/mm²

Specific Gravity $\approx 4.7 \text{ g/cm}^3$

The above quoted properties are typical for Fair-Rite MnZn and NiZn ferrites.

See next page for further material specifications.




Fair-Rite Products Corp. PO Box J,One Commercial Row, Wallkill, NY 12589-0288 Phone: (888) 324-7748 www.fair-rite.com

A new high frequency NiZn ferrite material, that combines a high saturation flux density and a high Curie temperature.


SM beads, PC beads and a range of rod cores are available in this material.

Complex Permeability vs. Frequency



Measured on a 17/10/6mm toroid using the HP 4284A and the HP 4291A.

Initial Permeability vs. Temperature



Measured on a 17/10/6mm toroid at 100kHz.

Fair-Rite Product's Catalog Part Data Sheet, 4052077111

Printed: 2013-07-03








52 Material Specifications:


Property	Unit	Symbol	Value
Initial Permeability ® B < 10 gauss		μ_{i}	250
Flux Density	gauss	В	4200
@ Field Strength	oersted	н	10
Residual Flux Density	gauss	B _r	2900
Coercive Force	oersted	н。	0.60
Loss Factor	10-6	tan δ/μ;	45
@ Frequency	MHz		1.0
Temperature Coefficient of Initial Permeability (20 -70°C)	%/°C		1.0
Curie Temperature	°C	Te	>250
Resistivity	Ωcm	ρ	1x10 ⁹

Flux Density vs. Temperature



Measured on a 17/10/6mm toroid at 10kHz. and H=10 oersted.

Hysteresis Loop



Measured on a 17/10/6mm toroid at 10kHz.